




Mortise Lock: SALTO LE8Pxx....

salto
INSPIRED ACCESS

salto
INSPIRED ACCESS

LOCK INSTALLATION

Eng

PREPARING THE DOOR

Note: if a strike is already fitted in the door frame, position the lock using the strike as reference.
(See strike position on template)

1. Draw a horizontal line on both sides and edge of the door at the desired height of knob above floor.
2. Draw a vertical centre line on door edge.
3. Draw a vertical line on each side at the proper backset to align the template.
4. Position templates on edge and sides of door. Mark **ONLY** top and bottom holes of mortise cavity (A) and lock front (B) on door edge, and holes in the lateral face of the door for handles (C) and turn piece (D) (only needed in inside face). If SALTO electronic escutcheon will be installed, mark the corresponding holes for its fixing (E). The (E) holes can be done afterwards with the template supplied using the electronic escutcheon.
5. Remove template: Place lock face against door edge. Trace outline of faceplate as guide for faceplate routing.

MORTISE THE DOOR

1. Mortise door for lock body and faceplate as per instructions on template.

INSTALLING THE LOCK BODY


1. Insert the lock into the cavity.
2. Mark & drill faceplate holes. Fasten with faceplate screws to hold lock in place.

INSTALLING THE STRIKE

1. Refer to latch to determine strike location on jamb.
2. Using strike as template, mark and chisel recess. Drill screw holes. Place dust box and strike and fasten screws.

Please check that:

- Deadbolt and latch fit the cavities of the strike without touching it.
- Gap between door and jamb is between 2-4 mm.
- Strike flap should protrude a minimum 2mm, if it does not, please ask your distributor for the availability of special strikes.



LE8P02xx

LE8P12xx



LE8P22xx

CE	1239 / CPR / 0802902	08	CERTIFIRE
UK	1239 / CPR / 0802902	08	CF 5652
EN 12209:2003 + AC:2005	3 M 2 1 0 F 0 B 0 1 0	22	LE8P02
EN 179:2008	3 7 6 8 1 3 3 2 A B D		
SALTO SYSTEMS, S.L. UK Importer: SALTO SYSTEMS, Ltd			
P.O. Box 1, Llanfair, Llanfair, Gwynedd, LL55 2AB, North Wales, UK			

CE	1239 / CPR / 0802902	08	CERTIFIRE
UK	1239 / CPR / 0802902	08	PANIC
EN 12209:2003 + AC:2005	3 M 2 1 0 F 2 B 0 1 0	22	LE8P12
EN 179:2008	3 7 6 8 1 3 3 2 A B D		
SALTO SYSTEMS, S.L. UK Importer: SALTO SYSTEMS, Ltd			
P.O. Box 1, Llanfair, Llanfair, Gwynedd, LL55 2AB, North Wales, UK			

CE	1239 / CPR / 0802902	08	CERTIFIRE
UK	1239 / CPR / 0802902	08	CF 5652
EN 12209:2003 + AC:2005	3 M 2 1 0 F 0 B 0 1 0	22	LE8P22
EN 179:2008	3 7 6 8 1 3 3 2 A B D		
SALTO SYSTEMS, S.L. UK Importer: SALTO SYSTEMS, Ltd			
P.O. Box 1, Llanfair, Llanfair, Gwynedd, LL55 2AB, North Wales, UK			

12 Holes
Depth 105 (4-9/64")




The LE8Pxx mortise lock is supplied as right hand (R), if your installation is left hand (L), as shown in the image, proceed to make the hand changing as indicated

Eng

HAND CHANGING


Please follow the drawing:

1. Press the auxiliary latch to project latch bolt.
2. Push the latch forward from the back of the lock with a screw driver until it completely comes out from the front then turn 180°.
3. Turn the lever to deactivate auxiliary latch.
4. Pull the auxiliary latch forward and turn it 180°.



Mortise Lock: SALTO LE8Pxx...

INSTALACION CE8Pxx/ STRIKE



** For the auxiliary latch to operate correctly, it is absolutely essential to install the dust box.

LUBRICATION

All locks come from the factory pre-lubricated with grease. We recommend, however, continued periodic lubrication of internal moving parts with commercial quality grease (every 20.000 cycles or once a year). This can prolong the life of the lockset by reducing excessive wear. If the lockset is used in a harsh environment, lubrication should be applied more frequently.

*EN 179: The security characteristics of this product are essential to meet the EN 179 standard. Modifications other than those described in these instructions are not permitted. It is for use on doors with maximum dimensions of 1300x2500mm (4.26'x8.2') and a weight of no more than 200kg (440lb). It only meets EN 179 when U or H handles are used.

UK IMPORTER CONTACT INFORMATION :

SALTO SYSTEMS, Ltd.
Unit 1, The Court Holywell Business Park, Northfield Road, CV47 0FS Southam, UK.